

## Product information

### mzr-Touch Control · Controller



#### Description

The control module mzr-Touch Control provides users in the laboratory and production area with a simple yet versatile dosing unit for precise delivery and dosing in the low-flow range. The combined drive and control unit allows the operation of micro annular gear pumps with the aid of touch operation as well as an external analog interface (0-10 V). The high-quality die-cast aluminum housing is powder coated and offers reliable protection of the operating and functional elements. The control module is supplied with 24 V DC via supplied power supply unit.

#### Advantages

- Compact housing  
aluminum die cast, powder coated
- Easy handling  
touch function, standardized plug, switch button
- Display  
illuminated Touch Display
- User friendly interfaces  
analog 0 10 V, digital input
- Integrated Motion Controller  
(type N only)
- For DC-motors and BLDC-motors  
with integrated Faulhaber Motion Controller

#### Applications

- Laboratory
- Assembly technology

## Technical data

Chassis	die-cast aluminum housing, powder coated
Operation	touch display 4.3"
Display	different graphical user interfaces e.g. discrete dosage, continuous dosage, terminal
Version	Type N: connection LP/MO pump series; Type H: connection HP/Hi/MH pump series; Type R: connection over RS-232 Interface
Serial interface (just Type R)	RS-232, SUB D male, 9-pole
Pump connector (just Type H)	8-pole socked (DIN 45326)
Motion Controller (just Type N)	integrated 16-Bit Microcontroller
Power source	24 V DC, 3-pole socket
Analog interface	0 – 10 V, 5-pole socket
Digital outputs	Open Collector, 24 V, 0.5 A
Degree of protection	IP 65
Dimensions (L x W x H)	147 x 141 x 37 mm
Weight	approx. 0.7 kg

### Notice

Even if single parameters are within the indicated performance range of technical data, certain parameter combinations may not be achievable. Single parameters may exceed their indicated performance range under adequate circumstances. For detailed evaluation please contact HNP Mikrosysteme. Actual performance may vary. Specifications are subject to change without notice.

## Other accessories

- Carrier frame for mZr-Touch Control and pump assemblies
- Input pen
- Hand switch or foot switch
- Clamp mountings
- Pump assemblies with filter and valves

## Patents and trademarks

Micro annular gear pumps (and housings) are protected by assigned patents: EP 1 354 135 B1; US 7,698,818 B2; DE 10 2011 001 041 B4; CN 103 348 141 B; US 10,012,220 B2; CN 103 732 921 B; US 9,404,492 B2; US 6,520,757 B1.

HNP<sup>®</sup>, mZr<sup>®</sup>, MoDoS<sup>®</sup>, µ-Clamp<sup>®</sup>, µDispense<sup>®</sup>, Centrifluidic Technologies<sup>®</sup>, LiquiDoS<sup>®</sup>, smartDoS<sup>®</sup>, ColorDoS<sup>®</sup> are registered German trademarks of HNP Mikrosysteme GmbH.

## Contact

HNP Mikrosysteme GmbH  
Bleicherufer 25  
19053 Schwerin  
Germany

T +49 385 52190-300  
F +49 385 52190-333  
info@hnp-mikrosysteme.de

Last update 2020/02